

# EXIT/DOORWAY MONITOR    PACKAGE/MAIL MONITOR VEHICLE MONITOR                    LAUNDRY MONITOR VERSATILE RADIATION CONTROL MONITOR

Model - FM-9W-V

## FEATURES:

- MULTI-CHANNEL SYSTEM (MCA)
- ON-BOARD DATA ARCHIVE & RETRIEVAL
- STOP ENTRY/EXIT OF RADIOACTIVE ITEMS
- HIGHLY SENSITIVE
- 50 DETECTOR MODELS
- ALARMS WITH RADIATION DETECTION
- RELAY CONTROL CAN LOCK DOORS, TRIGGER A SIREN OR SEND AN ALERT



TABLE TOP  
ELECTRONICS



WALL MOUNT  
ELECTRONICS

## DESCRIPTION:

FM-9W-V radiation control monitors are rugged and ideal for either laboratory or industrial application. AC Operation. These versatile instruments fill a varied list of applications and placement needs.

The FM-9W-V series utilize a variety of probes including Technical Associates P & S series, Geiger, and scintillation. The many choices in probes provide instrumentation that will fit your need.

- User settable to preferred engineering units: mR/h; Sv/h, microCuries/ml, etc.
- Computer interface, USB, Ethernet, etc,

## APPLICATION:

Maintain control of radioactive materials through monitoring when and where radioactive materials are entering or leaving an area. The FM-9W-V has many variations including the highly sensitive FM-9W-V/PGS-3 and the FM-9W-V/PGS-3L. These instruments are easily placed at entrances, exits, and other strategic locations monitoring:

## DETECTORS:

**Probe Holder:** Probe Holder is provided for probe purchased.

**Any GM** (such as P-13, P-15, P-6LB, etc.) or

**Alpha, Beta, Gamma or Neutron Scintillator** (such as PAS-8, PAS-9, PGS-3, PGS-3L, PNS-19, etc.).

**NOTE:** PGS-3:                    1"x1" diameter NaI crystal  
                  PGS-3L:                    2"x1" diameter NaI crystal



**TECHNICAL ASSOCIATES  
OVERHOFF TECHNOLOGY**

7051 Eton Ave., Canoga Park, CA 91303  
818-883-7043 (Phone) 818-883-6103 (Fax)

[tagold@nwc.net](mailto:tagold@nwc.net)

[WWW.TECH-ASSOCIATES.COM](http://WWW.TECH-ASSOCIATES.COM)

Divisions of



US NUCLEAR CORP

# EXIT/DOORWAY MONITOR    PACKAGE/MAIL MONITOR VEHICLE MONITOR                      LAUNDRY MONITOR VERSATILE RADIATION CONTROL MONITOR

Model - FM-9W-V

	FUNCTION	DETECTS Alpha, Beta, Gamma Unless Otherwise Noted	PLACEMENT
1	EXITS / DOORWAYS	Alarms when radioactivity is carried through an exit or doorway.	Mount to top or side of door frame or mount to wall adjacent to doorway.
2	HANDS & SHOES	Checks hands and shoes for contamination	Floor standing cabinet or wall and table mounted.
3	VEHICLES	Alarms when vehicle carrying radioactivity stops at guard house.	Mount on posts on either side of facility entrance road. Requires weather-proof probe housing and long cables.
4	LAUNDRY	Detects contaminated garments.	Mount above sorting table or conveyor belt.
5	FUME HOODS	Alarms when radioactivity is released into fume hood exhaust.	Mount inside or on top of fume hood filter enclosure.
6	MOBILE RADIATION LABORATORY	Measures radiation from fixed sources or from other vehicles	Small unit sits in front seat or trunk. Larger unit slides into rear of van or truck.
7	PACKAGE / MAIL	Checks mail and packages.	Mount to sorting table, mail conveyor, or door frame of entry for mail.
8	LOADING DOCK / WASTE ROOM/COMPACTER	Checks packages and waste.	Mount to loading dock receiving area, conveyor, or door frame of entry.
9	CAM-AIR / STACK	Tests stack gases, room air, etc. for a variety of contaminants..	Mounted in rack or wheeled cabinet. Includes detectors, shields, and pumps.
10	REAL-TIME DRINKING WATER	Measures alpha, beta, gamma to EPA PAG protective action level.	Free standing cabinet.
11	LIQUID SCINTILLATION	Highly sensitive alpha-beta-Gamma or Tritium LSC Systems	Lab, bench model or portable unit mounted in carrying case.
12	MULTI-DETECTOR AREA	Gamma or PET or Neutron	Wall mounted detectors, local/remote display and alarms.
13	MULTI-DETECTOR ARRAY	Indoor or outdoor system	As needed to fit specific use.
14	REAL-TIME WATER OR LIQUID EFFLUENT	Test liquid discharge from pipe discharge channel, soil, or pond.	Systems available with submersible probe or with real-time continuous sampling pump.



## TECHNICAL ASSOCIATES OVERHOFF TECHNOLOGY

7051 Eton Ave., Canoga Park, CA 91303  
818-883-7043 (Phone) 818-883-6103 (Fax)

[tagold@nwc.net](mailto:tagold@nwc.net)

[WWW.TECH-ASSOCIATES.COM](http://WWW.TECH-ASSOCIATES.COM)

Divisions of



US NUCLEAR CORP

# EXIT/DOORWAY MONITOR    PACKAGE/MAIL MONITOR VEHICLE MONITOR                    LAUNDRY MONITOR VERSATILE RADIATION CONTROL MONITOR

Model - FM-9W-V

## SPECIFICATIONS:

### ELECTRONICS:

<b>Engineering Units:</b>	User can input correct conversion factor and change to any units.
<b>Controls: Front Panel:</b>	On-Off, Alarm-mute, Rate, Integrate, Reset.
<b>Recessed or Internal:</b>	Discriminator level, high voltage. Other adjustable settings: See calibration.
<b>Input Sensitivity:</b>	Adjustable from less than 1 millivolt to 100 millivolt Anti-saturation and Dead-time Corrections are available.
<b>Alarm:</b>	2000 Hz audio tone with audio "mute" switch + RED LIGHT High current relay. 0-100% of full scale.
<b>Alarm Set Point:</b>	User settable to any point on the detector range.
<b>Serial Output:</b>	Two way USB standard, Ethernet optional.
<b>Power:</b>	105-125 volts, 50-60 Hz (220 V optional)
<b>Construction:</b>	Gasketed aluminum case.

### DIMENSIONS & WEIGHT:

13.5" W X 11" H X 3.6" D (25 cm x 18 cm x 10cm), excluding probe holder, feet, and knobs.  
3 pounds (1.4 kg) including batteries and hardware, excluding probe.

**SEE PROBE SELECTION BELOW**



**TECHNICAL ASSOCIATES**  
**OVERHOFF TECHNOLOGY**

7051 Eton Ave., Canoga Park, CA 91303  
818-883-7043 (Phone) 818-883-6103 (Fax)

[tagold@nwc.net](mailto:tagold@nwc.net)

[WWW.TECH-ASSOCIATES.COM](http://WWW.TECH-ASSOCIATES.COM)

Divisions of



US NUCLEAR CORP

# EXIT/DOORWAY MONITOR    PACKAGE/MAIL MONITOR VEHICLE MONITOR                    LAUNDRY MONITOR VERSATILE RADIATION CONTROL MONITOR

Model - FM-9W-V

CHOOSE ANY TA OR COMPATIBLE PROBE



•Over 50 different T/A probes and sample counter detectors  
Probe holder supplied - no charge if probe and FM-9W purchased together

DESCRIPTION	RADIATION DETECTOR
A. PG-LB. Low Background GM	Alpha, Beta, Gamma, X-ray
B. PAS-9. 100 cm <sup>2</sup> Scintillator	Alpha
C. PGS-3 Scintillator	Beta, Gamma
D. COL-3S Collimator	NA
E. PLS-04. Wound Monitor	Pu-239
F1. IC-1 Ion Chamber F2. IC-2 Ion Chamber F3. DMU-1000. Submersible Ion-Chamber	Beta, Gamma, X-Ray Gamma Area Monitor Nuclear Plant Fuel Rods
G. P-15. Surface Monitor GM	Alpha, Beta, Gamma, X-ray
H. STB-TF-6. Sample Counter	Tritium, C-14
I. TS-26. Surface Monitor	Tritium, C-14
J. PN-13. Rem Ball	Neutrons
K. Silicon (Not Shown)	High Flux Beta - Gamma



**TECHNICAL ASSOCIATES  
OVERHOFF TECHNOLOGY**

7051 Eton Ave., Canoga Park, CA 91303  
818-883-7043 (Phone) 818-883-6103 (Fax)

[tagold@nwc.net](mailto:tagold@nwc.net)

[WWW.TECH-ASSOCIATES.COM](http://WWW.TECH-ASSOCIATES.COM)

Divisions of  US NUCLEAR CORP