



FM-9-BG Electronics

# Beta – Gamma Particulate Air Monitor

Model Series; FM-9-ABGN

Model FM-9-ABGN and Model FM-9-ABGN-C

## Features

- Detects Beta and Gamma Particulates Including Mo-99, Cs-137, K-40
- Airborne Concentration
- Integrated Exposure
- High Sensitivity
- **Optional:** Cyclone Particle Separator (**FM-9ABGN-C**)
- Real Time Alarm
- Line Operated
- Bench Top
- Standard FM-9 Modules
- Can Draw Air From Hood, Duct, etc.
- Quick Change Filter Cartridge
- Real Time Air Flow Measurement Display
- Data Archive and Retrieval
- Computer Interface – USB or Ethernet

## Application

The **FM-9-ABGN** Air Monitor assure safety against airborne radioactivity contamination by means of constant check with alarm and record capability. It provides integrated exposure information with an optional hard copy via external printer or computer.

It is a complete system but may be expanded per need with modules of the **FM-9** series.

The **FM-9-ABGN** is sensitive and versatile.

The **FM-9-ABGN-C** has the Optional cyclone particle separator particles are pre-sorted prior to moving through the Beta Particulate Detector. The particle size of separation is for 2.5 and 10 microns.

It may be used to monitor stack effluent down to EPA levels as well as hoods, glove box or workplace air.

## Description

The **FM-9-ABGN** uses a standard filter in TA's unique quick change, no leak holder to trap any airborne particulates. The filter is under constant surveillance via a thin window GM pancake detector.

Air is drawn by a regulated pump through a three-foot inlet hose and exhausted via a flow meter through another three-foot hose. These may be extended to allow monitoring of hoods, glove boxes, stacks, etc.

Time is recorded by a computer wired into the pump circuit.

The unit is completely self-contained and portable. Complete with box of 100 filters.



## TECHNICAL ASSOCIATES OVERHOFF TECHNOLOGY

7051 ETON AVENUE, CANOGA PARK, CALIFORNIA 91303

PHONE: 818-883-7043 | FAX: 818-883-6103

SALES@TECH-ASSOCIATES.COM | TECH-ASSOCIATES.COM | USNUCLEARCORP.COM

DIVISIONS OF



USNUCLEARCORP

OTCQB-UCLC

# Beta – Gamma Particulate Air Monitor

**Model Series; FM-9-ABGN**

**Model FM-9-ABGN and Model FM-9-ABGN-C**

## Specifications

**Sensitivity:** Limit of sensitivity at 120 liters/minute air flow rate is  $4 \times 10^{-13}$   $\mu\text{Ci/cc}$  integrated over an 8 hour period, or  $8 \times 10^{-14}$   $\mu\text{Ci/cc}$  for a 40 hour period.

This corresponds to  $2 \times 10^{-10}$   $\mu\text{Ci/ml}$  minute exposure equal to 0.6% of the California Safety Code Title 17 and USNRC Title 10 limit for 40 hour weekly exposure to most hazardous Beta and/or Gamma emitter in absence of Ac 227.

**Detector:** 2" diameter thin window GM detector Model T-1190  
Sensitivity to ALL Beta-Gamma positron emitters including: Mo-99, Cs-137, K-40.

### Electronic Modules Include:

**MV-5.12.24:** Power Supply  
**MAC-9:** Air Control Timer; Low Flow Alarm Flowmeter  
**FM-9:** On Board computer with color monitor  
**M $\mu$ P:** Imbedded processor

**Range:**  $1 \times 10^{-13}$  to  $1 \times 10^{-7}$   $\mu\text{Ci/cc}$  or  $(\text{Ci/m}^3)$  depends on count time and flow rate.

**Alarm:** Settable 2000 Hz beeper and red flasher.

**Response Time:** Settable 1 second to 40 hours.

**Readout:** 7" Color LCD monitor built-in for digital and graphic user data display.

**Flow Rate:** Normally set at 70 liters/min.

**Mass Flow Meter:** Real-Time air flow rate data feeds directly into data analyzer software and embedded processor for highest concentration accuracy.

**Power:** 115V, 50-60 Hz (**Optional** 230 V).

**Shielding:** 1" lead about sample and detector.

**Pump:** Muffler and trap included. 115V 60Hz 2A. (230 V 50-60 Hz optional).

**Filters:** Includes box of 100 glass fiber filters – 2" or 55mm.

Can also use membrane, paper or glass fiber filters.

**Case:** Electronics housed in enameled aluminum case; carrying handles optional.

### Weight and Dimensions:

**Dimensions:** Electronics: Excluding pump and detector assembly: 20" W x 13" H x 18" D.

Detector Assembly: 5" W x 10" H x 6" D.

Cyclone Separator: 1 ounce

Pump Assembly: 8" W x 8" H x 14" D.

Shipping Weight: 84 lbs.



**TECHNICAL ASSOCIATES  
OVERHOFF TECHNOLOGY**

7051 ETON AVENUE, CANOGA PARK, CALIFORNIA 91303

PHONE: 818-883-7043 | FAX: 818-883-6103

SALES@TECH-ASSOCIATES.COM | TECH-ASSOCIATES.COM | USNUCLEARCORP.COM

DIVISIONS OF  
 USNUCLEARCORP  
OTCQB-UCLE

# Beta – Gamma Particulate Air Monitor

Model Series; FM-9-ABGN


Model FM-9-ABGN and Model FM-9-ABGN-C

Accessories: Filter - Free flowing glass fiber filters – 2" or 55mm.

DESCRIPTION	FM-9-ABGN & FM-9-ABGN-C
Read-Out Units	$\mu\text{Ci/cc}$
<b>Optional</b> Read-Out Units	Specify at Time of Order
Measures	Airborne Concentration
Smart System	Calculations by Imbedded Processor On Board: Data Archive, Display, Download
<b>Special Feature</b>	Electronic Mass Flowmeter



Oil-Less Green Turtle Pump



FM-9ABGN-C Flow Chart



**TECHNICAL ASSOCIATES**  
**OVERHOFF TECHNOLOGY**

7051 ETON AVENUE, CANOGA PARK, CALIFORNIA 91303

PHONE: 818-883-7043 | FAX: 818-883-6103

SALES@TECH-ASSOCIATES.COM | TECH-ASSOCIATES.COM | USNUCLEARCORP.COM

DIVISIONS OF  
 USNUCLEARCORP  
OTCQB-UCLC